

USB Dual Docking Station for 2 x SATA HDD / SSD with Clone Function and Card Reader + additional USB Port

Description

This docking station by Delock enables an external connection of up to **two 2.5" or 3.5" SATA HDDs or SSDs** through the USB interface. This solution does not require an external enclosure since the drive can be plugged into the docking station directly. Furthermore the **clone function** enables to copy the content of one HDD to another without using a PC.



Integrated Card Reader

In addition, the docking station with integrated card reader expands a PC or laptop by an **SD and a Compact Flash** slot via the USB connection.

Additional USB Type-A port

Thanks to the additional USB Type-A female, no USB socket is blocked on your computer, because it can still be used for USB memory or other USB devices.

Item no. 64183

EAN: 4043619641833

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB 5 Gbps (USB 3.2 Gen 1) Type-B female
 - 2 x SATA 6 Gb/s 22 pin receptacle
 - 1 x SD slot
 - 1 x Compact Flash slot
 - 1 x SuperSpeed USB 5 Gbps (USB 3.2 Gen 1) Type-A female
 - 1 x DC jack
- Chipset: VIA VL813, JMicron JMS561U
- Function key:
 - 1 x Clone button
 - 1 x On / Off switch
- For 2.5" and 3.5" SATA HDD / SSD
- Suitable for all SATA HDDs up to SATA 6 Gb/s
- It can only be used one memory card, not both at the same time
- Data transfer rate up to 5 Gbps
- LED indicator for power, access and copy status

- Dimensions (LxWxH): ca. 153 x 110 x 62 mm
- Plug & Play

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 1.5 A
- Output: 12.0 V / 3.0 A
- Ground outside, plus inside
- Dimensions:
 - inside: ø ca. 2.1 mm
 - outside: ø ca. 5.5 mm
 - length: ca. 10 mm

System requirements

- Android 11.0 or above
- Chrome OS
- Linux Kernel 5.11 or above
- Mac OS 12.0.1 or above
- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- Docking station
- Cable USB Type-A male to Type-B male, length ca. 80 cm
- External power supply 12.0 V / 3.0 A
- User manual

Images



General

Function:	Clone Function
Suitable for data medium:	2.5" 3.5" SSD or HDD
Supported operating system:	Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11 Linux Kernel 5.11 or above Mac OS 12.0.1 or above Android 11.0 or above

Interface

External:	1 x CF slot 1 x SD slot 1 x DC 12 V power connector 1 x USB 5 Gbps Type-A female 1 x USB 5 Gbps Type-B female
Internal:	2 x SATA 22 Pin Buchse

Technical characteristics

Chipset:	VIA VL813 JMicron JMS561U
----------	------------------------------

Physical characteristics

Housing material:	Plastic
Length:	153 mm
Width:	110 mm
Height:	62 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de