



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		A	-	04FEB2002	-	-

Kontakt Contact	DGB (mm ²) Wire Range	Drahtcrimp/Wirecrimp		Isocrimp	Iso.-∅ Ins. Range	Betriebsanl. Instr. Sheet
		Hoehe/Height	Breite/Width	Breite/Width		
964279 / 964291	0.2-0.5	1.01	1.58	2.30	1.0-1.6	411-18137
964283 / 964293	0.5-1.0	1.21	2.03	2.54	1.4-2.3	
964295 / 964346	1.5-2.5	1.61	2.54	3.60	2.1-3.1	



539664-2	1	0-539786-1	contact guide	Kontaktabstuetzung	A
	1	8-539634-5	screw M4x11	Schraube M4x11	A
	1	8-539634-6	screw M4x18	Schraube M4x18	A
	1	0-519021-8	hex nut M4	Mutter M4 DIN 934	A
	QTY Stck	PN	Description	Benennung	REV

DIMENSIONS: mm-DIN 7168-m		DWN D.Reissig 01FEB2000	MATERIAL -		FINISH -			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		CHK U.Reuter 01FEB2000	AMP tyco Electronics AMP GmbH D - 64625 Bensheim					
		APVD -						
		PRODUCT SPEC -	NAME ERGOCRIMP Die Set for Junior Power Timer					
		APPLICATION SPEC -						
		WEIGHT -	SIZE A 4	CAGE CODE 00779	DRAWING NO C=539664-2	RESTRICTED TO -		
		CUSTOMER DRAWING		SCALE 2:1	SHEET 1	OF 1		
				REV A				