
LF = Lead-free Test Probes


mm [inch]



LF1000 LF53 M

Minimum centers:	2.54 [.100]
Full travel:	6.35 [.250]
Working travel:	4.00 [.157]
Current rating:	5 A
Probe resistance:	< 100mΩ
Operating temperature:	-50°C up to +150°C
Plunger material:	Steel / Gold plated
Barrel material:	PhBr / Gold plated
Spring material:	Stainless steel

Spring force at working stroke: 2.0 N [7.2 oz]



© COPYRIGHT 2023
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	M.K.	2023.11.02
Drawed		
Checked		
Note		

Catalog Item: **LF1000 LF53 M**

Drawing No.:

A4 SHEET 1 OF 1

EQUIP TEST
TEST - SUPPORT - INNOVATE