

# Pushbutton, 15.2 mm, screw connector, momentary contact function, 1 NO, bezel green



## Description

Pushbutton with mounting hole diameter 15.2 mm

Pushbutton with mounting hole diameter 15.2 mm, screw terminal



## technical data

### > general

|                                                             |                               |
|-------------------------------------------------------------|-------------------------------|
| Bezel color                                                 | green                         |
| Property of bezel / mushroom                                | opaque                        |
| Collar shape                                                | round                         |
| Operating temperature, min.                                 | -25 °C                        |
| Operating temperature, max.                                 | 85 °C                         |
| Storage temperature, min.                                   | -40 °C                        |
| Storage temperature, max.                                   | 90 °C                         |
| illuminated                                                 | No                            |
| Packaging                                                   | Box                           |
| Packaging unit                                              | 100 pcs.                      |
| Net weight                                                  | 5 g                           |
| Operating life                                              | 25,000 cycles                 |
| B10                                                         | 32,500 cycles                 |
| Degree of protection, front side, according to DIN EN 60529 | IP40<br>IP65 with sealing cap |
| Minimum order quantity (MOQ)                                | 100 pcs.                      |
| RoHS compliant                                              | Yes                           |
| REACH compliant                                             | Yes                           |
| Country of origin                                           | HU                            |

### direct links

> [RAFI eCatalog](#)

### > mounting diameters

|                          |         |
|--------------------------|---------|
| Outside dimension, width | 19 mm   |
| Mounting hole            | 15.2 mm |
| Mounting depth           | 21.5 mm |
| Installation height      | 8.2 mm  |

### > mechanical data

|                        |                            |
|------------------------|----------------------------|
| Terminal on the rear   | Screw terminal             |
| Fixing                 | Threaded ring              |
| Actuation function     | momentary contact function |
| Operating force, max.  | 7.5 N                      |
| Operating travel, max. | 3 mm                       |
| Contact function       | 1 NO                       |

|                  |                |
|------------------|----------------|
| Contact system   | Bridge contact |
| Contact material | Silver         |

**> electrical data**

|                     |       |
|---------------------|-------|
| Rated voltage, max. | 250 V |
| Rated current, max. | 0.7 A |