

# USB Type-C™ DP 1.4 Docking Station Triple 4K Display - HDMI / DisplayPort / USB / LAN / SD / PD 3.0

## Description

This docking station by Delock can be connected to a computer with a **USB-C™ DP Alt Mode** or **Thunderbolt™ 3** port and provides a variety of interfaces. Up to three monitors can be operated simultaneously at the DisplayPort and HDMI outputs. Four built-in USB ports allow the use of peripherals, connections for headset and Gigabit network, as well as SD and Micro SD slot complete the features.

### Multi-Stream Transport (MST)

The product is an MST hub and supports the extended desktop configuration of DisplayPort. This allows **multiple monitors to be combined into one large display**. The maximum resolution for simultaneous playback on two or three monitors depends on the system and connected hardware.

### USB Power Delivery (USB PD 3.0) support up to 85 watt

The docking station has a **USB Type-C™ Power Delivery port** to connect the power supply of the laptop or tablet to charge it.

### Stand

The Delock docking station can be operated either **horizontally or vertically**. A stand is included for vertical operation.

[Delock USB Type-C™ DP 1.4 Docking Station Triple 4K Display](#)

## Please Note

If the docking station is connected to a USB-C™ DP Alt Mode port with DP 1.2, not all display functions are available. Therefore, the connection to DP 1.4 is recommended.

Under Windows, only one display can be duplicated to the main screen, the other displays can either be expanded or duplicated with each other as an extension to the main screen.



**Item no. 87772**

EAN: 4043619877720

Country of origin: China

Package: Retail Box

## Technical details

- 4 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ female >
- 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ female
- 1 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female - Battery Charging specification BC1.2
- 2 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female
- 1 x HDMI-A female
- 2 x DisplayPort female
- 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
- 1 x Headset 3.5 mm 4 pin jack
- 1 x SD slot
- 1 x Micro SD slot

- Max. resolution (depending on the system and the connected hardware):

with DSC:	
Single Display	HDMI: 3840 x 2160 @ 60 Hz DP: 5120 x 2880 @ 60 Hz
Dual Display SST	HDMI + DP: 2 x 3840 x 2160 @ 60 Hz DP + DP: 2 x 5120 x 2880 @ 60 Hz
Triple Display SST	HDMI + 2 x DP: 3 x 3840 x 2160 @ 60 Hz
Dual Display MST	HDMI + DP: 2 x 3840 x 2160 @ 60 Hz DP + DP: 2 x 3840 x 2160 @ 60 Hz
Triple Display MST	HDMI + 2 x DP: 3840 x 2160 @ 60 Hz + 2 x 3840 x 2160 @ 30 Hz

without DSC:	
Single Display	HDMI: 3840 x 2160 @ 60 Hz DP: 3840 x 2160 @ 60 Hz
Dual Display SST	HDMI + DP: 2 x 3840 x 2160 @ 60 Hz DP + DP: 2 x 3840 x 2160 @ 60 Hz
Triple Display SST	HDMI + 2 x DP: 3 x 3840 x 2160 @ 60 Hz
Dual Display MST	HDMI + DP: 2 x 3840 x 2160 @ 30 Hz DP + DP: 2 x 3840 x 2160 @ 30 Hz
Triple Display MST	HDMI + 2 x DP: 3840 x 2160 @ 30 Hz + 2 x 1920 x 1080 @ 60 Hz

- Supported refresh rates (depending on the operating system)

## Power supply specification

- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.8 A
- Output: 12 V / 2 A
- Ground outside, plus inside
- Dimensions:
  - inside: ø ca. 2.5 mm
  - outside: ø ca. 5.5 mm
  - length: ca. 10 mm

## System requirements

- Android 9.0 or above
- iPad Pro (2018)
- Mac OS 10.15.5 or above
- Windows 8.1/8.1-64/10/10-64/11
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 port

## Package content

- USB-C™ docking station
- Cable USB-C™ male to USB-C™ male, length ca. 50 cm
- Stand
- Power supply
- User manual

## Images



## General

Function:	HDR / HDR10 mirror and extend
Supported operating system:	Android 9.0 or above Mac OS 10.15.5 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018)

## Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

## Physical characteristics

Length:	180 mm
Width:	77 mm
Height:	18 mm
Colour:	grey

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de