
C1-15 BATTERY CHARGER





FEATURES

* RATING : 12V DC
* Charging current: 900mA/AA, 400mA/AAA
* Fast charging time: 2.5 hrs.
* MATERIAL :
  Housing : ABS (UL flame: 94-HB 105˚C).
  Top contact : nickel plated brass.
  Spring contact : nickel plated spring steel.
* Reverse polarity protection.
* LED charging indicator: Red=Charging, Green=Fully Charged.
* LED light flashes when charging non-rechargeable or bad batteries.
* Charge operating for dual-battery loading only.
* Adjustable tab for adapting to charging AA or AAA batteries(Batteries not included).
* Adjustable side contacts for adapting 21 or 22 mm dia. of cigarette lighter socket.
* Push on-off switch at the side to light up build-in LED flash light at the bottom while loading alkaline batteries or rechargeable batteries.
* C1-15: Without LED flash light.
* C1-15B: With LED flash light.