

VS-15-DSUB-20-LI-5,0 - D-SUB cable

1656288

<https://www.phoenixcontact.com/gb/products/1656288>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled D-SUB cable shielded, 15-pos., stranded (7-wire), cable color RAL 7000 (gray), IP20 degree of protection, head 1 with socket shell 2 and straight cable outlet, head 2 with pin shell 2 and straight cable outlet, length: 5 m

Commercial data

Item number	1656288
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABNCAS
Product key	ABNCAS
GTIN	4046356029766
Weight per piece (including packing)	333.9 g
Weight per piece (excluding packing)	295.6 g
Customs tariff number	85444290
Country of origin	CN

VS-15-DSUB-20-LI-5,0 - D-SUB cable



1656288

<https://www.phoenixcontact.com/gb/products/1656288>

Technical data

Product properties

Product type	Data cable preassembled
Type	D-SUB
Sensor type	Universal
Number of positions	15
Cable outlet	straight

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated current	1 A
Operating voltage	30 V
Transmission medium	Copper

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 50
-----------------------------	------

Material specifications

Housing material	PVC
Contact material	Copper alloy
Contact surface material	gold-plated
Outer sheath, material	PVC

Connection data

Connection technology

Connection method	D-SUB
-------------------	-------

Conductor connection

Connection method	D-SUB
-------------------	-------

Connector

Connection 1

Type	Socket straight D-SUB 15
Degree of protection	IP20

Connection 2

Type	Plug straight D-SUB 15
Degree of protection	IP20

VS-15-DSUB-20-LI-5,0 - D-SUB cable

1656288

<https://www.phoenixcontact.com/gb/products/1656288>



Cable/line

External cable diameter	28.00 mm
Outer sheath, material	PVC
External sheath, color	beige
Single wire, cross section	28 mm ²
Cable cross section	0.08 mm ²
AWG signal line	28
Shielding	Aluminum-coated foil, tinned copper braided shield

VS-15-DSUB-20-LI-5,0 - D-SUB cable


1656288

<https://www.phoenixcontact.com/gb/products/1656288>




Drawings

Schematic diagram



Connector pin assignment

Schematic diagram



Pin connector pattern


VS-15-DSUB-20-LI-5,0 - D-SUB cable



1656288

<https://www.phoenixcontact.com/gb/products/1656288>

Circuit diagram



Circuit diagram

VS-15-DSUB-20-LI-5,0 - D-SUB cable

1656288

<https://www.phoenixcontact.com/gb/products/1656288>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1656288>



EAC

Approval ID: 19060508

VS-15-DSUB-20-LI-5,0 - D-SUB cable

1656288

<https://www.phoenixcontact.com/gb/products/1656288>



Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27440322

ETIM

ETIM 10.0	EC001132
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

VS-15-DSUB-20-LI-5,0 - D-SUB cable

1656288

<https://www.phoenixcontact.com/gb/products/1656288>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk