

Eaton 500NHG3B

Catalog Number: 500NHG3B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 500A, 120 kAIC, Combination fuse status indicator, fuse, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Ceramic body



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	500NHG3B
Packing Unit	
Pack	
Case Pack	
Quantity	
3	
12	
Gross Weight	Length
3.293 kg	240 mm
14.197 kg	330 mm
Width	Height
152 mm	95 mm
265 mm	210 mm
Volume	ERP Name
3465.6 cm ³	SAP-UNITY
18364.5 cm ³	SAP-UNITY
Product Length/Depth	Product Height
150 mm	86 mm
Product Width	Product Weight
71 mm	1027 g

	Compliances	Certifications
	RoHS Compliant	IEC 60269-1
defaultTaxonomyAttributeLabel	Do pobrania	
		DIN 43620

Type

fuse

Special features

Live gripping lug

Application

- industrial
- Utilities, Solar, Wind

Amperage Rating

500 A

Fitted with:

Metal gripping lugs

Fuse size

NH01

Current type

AC

Breaking capacity

120 kA

Frequency rating - max

62 Hz

Frequency rating - min

45 Hz

Rated switching capacity

120 kA

Rated voltage AC

500 V

Class

Class gG/gL

Fuse type

Square body with knife blade contact

Utilization category

gL/gG (cable protection/equipment protection)

Interrupt rating

120 kAIC

Fuse indicator

Combination fuse status indicator

Insulated metal gripping lugs (IMGL)

No

Connection

Blade end

Construction

NH3

Construction size

NH3

Fuse shape

Knife blade contacts

Square body

Voltage type

AC

Suitable for

Microswitch 170H0235

Material

Ceramic body

Quantity

3

Voltage rating

500 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.
All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia