



BETA 7340G

RENEGADE mesh fabric shoe, highly breathable, with traditional lacing



Certifications and Standards

CE S1PS FO SR HRO EN ISO 20345:2022

Features

The 7340G safety footwear focuses on breathability, comfort and design, ensuring wellbeing and style throughout the working day

SAFETY WITH STYLE

The shoe that offers protection without sacrificing looks.

Thanks to the "urban" style, inspired by sports shoes, it is also perfect to wear after work.

EXTREME COMFORT

Renegade combines advanced cushioning and superior support to provide exceptional comfort throughout the working day.

Thanks to its innovative design and high performance, it ensures a smooth and comfortable walk.

WIDE FOOTBED

The wide fit further enhances the comfort of the shoe, preventing possible constriction of the foot at any time of day.

BREATHABLE AND RESISTANT

The mesh upper, thanks to its open construction, offers exceptional lightness and optimal breathability. Its remarkable durability makes it perfect for ensuring a long life without compromising on quality.



INNOVATIVE DESIGN

The 7340G shoe combines sporty design and modern style, highlighting an innovative outsole that guarantees safety and comfort with every step



TRADITIONAL LACING

With traditional lacing, the laces can be adjusted for a secure and customised fit, ensuring perfect comfort with every step.



MAXIMUM RESISTANCE

The rubber outsole makes the shoe extremely durable and heat-resistant up to 300°C.



Certifications and Standards

CE S1PS FO SR HRO EN ISO 20345:2022



Specifications

LACING: traditional
WEIGHT (INDICATIVE SIZE 42): 495 g
TYPE: low

Lightness

- Highly breathable mesh fabric with TPU (thermoplastic polyurethane) inserts
- Heel stability support
- Traditional lacing

Comfort

- EVA (ethylene vinyl acetate)
- Durable nitrile rubber tread

Safety

EVA FOAM underfoot cover

Protections

Tip: Polymer material, 200 joules
Durability: Composite fibre, ceramic treatment

Coded items

	Art.	EU	UK	 mm
073400637	7340G 37	37	4,5	248
073400638	7340G 38	38	5	254
073400639	7340G 39	39	6	261
073400640	7340G 40	40	6,5	268
073400641	7340G 41	41	7	274
073400642	7340G 42	42	8	281
073400643	7340G 43	43	9	288
073400644	7340G 44	44	10	294
073400645	7340G 45	45	10,5	301
073400646	7340G 46	46	11	308
073400647	7340G 47	47	12	314
073400648	7340G 48	48	13	321

