



Click [here](#) for the 3D model.

Dimensions	
D	27mm MAX
H	20mm MAX
LL	15mm +/-2mm
S	15mm
S1	15mm
Wire Size	0.55mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	500
Typical Component Weight	18.5 g

General Information	
Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	6.2 mH (1 kHz)
Current	2 A
Temperature Range	-40/+120°C
DC Resistance	180 mOhms