



BETA 7352B

0-Gravity lightweight mesh fabric shoe, highly breathable



Certifications and Standards

CE S1PL FO SR HRO EN ISO 20345:2022

Features

The 7352B features a mesh upper and offers a combination of comfort, style and safety

LIGHTNESS

The 0-Gravity shoe weighs approximately 100g less than the average work shoe. The approximate weight is 450g (measured on size 42)

ALL-DAY COMFORT

The cushioning effect of the outsole makes walking less tiring. Greater comfort thanks to the wide fit and traditional lacing.

INNOVATIVE DESIGN

Blue colouring and attractive design give the shoe an innovative touch

BREATHABLE

The mesh upper is incredibly lightweight thanks to the open weave that promotes air circulation.



EVA FOAM UNDERFOOT COVER

The EVA underfoot cover, with a shock-absorbing heel pad, offers the perfect balance of support and comfort.



SLIP-ON COLLAR

Elasticised slip-on collar is designed for easy donning



DESIGN AND STYLE

Safety does not go unnoticed, thanks to the special details on the upper.



Certifications and Standards

CE S1PL FO SR HRO EN ISO 20345:2022



Specifications

LACING: traditional
 WEIGHT (INDICATIVE SIZE 42): 450 g
 TYPE: low

Lightness

EXTREMELY LIGHT - approximate weight for size 42: 450 grams

Comfort

Underfoot cover: EVA (Ethylene-Vinyl Acetate) FOAM with cushioning heel pad



Safety

Toe cap: polymer material, 200 joules
 Penetration-proof insole: composite fibre, ceramic treatment

Protections

- Tip:
- Highly breathable mesh fabric with TPU (Thermoplastic Polyurethane) inserts
 - Heel stability support
 - Stretch slip-on collar
- Durability: Outsole:
- EVA (Ethylene-Vinyl Acetate) midsole
 - Durable nitrile rubber tread

Coded items

	Art.	EU	UK	 mm
073520138	7352B 38	38	5	254
073520139	7352B 39	39	6	261
073520140	7352B 40	40	6,5	268
073520141	7352B 41	41	7	274
073520142	7352B 42	42	8	281
073520143	7352B 43	43	9	288
073520144	7352B 44	44	10	294
073520145	7352B 45	45	10,5	301
073520146	7352B 46	46	11	308
073520147	7352B 47	47	12	314
073520148	7352B 48	48	13	321

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

