

Antenna Cable RP-SMA jack bulkhead to I-PEX Inc., MHF® 4 plug 0.81 20 cm thread length 9 mm splash proof

Description

This antenna cable by Delock is suitable to supply an antenna signal in the interior of a device.

Due to the loose sealing ring on the base plate on the RP-SMA panel socket ensures a splash-proof connection to the unit.



Item no. 12460

EAN: 4043619124602

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RP-SMA jack bulkhead >
 - 1 x I-PEX Inc., MHF® 4 plug
- Thread length: 9 mm
- Impedance: 50 Ohm
- Cable: coaxial
- Cable type: 0.81
- Cable attenuation: 4.9 dB @ 2.4 GHz per meter
- Cable diameter: ca. 0.81 mm
- Smallest bending radius: 3.24 mm
- Cable colour: black
- Cable length incl. connectors: ca. 20 cm

System requirements

- Device with one free RP-SMA or I-PEX Inc., MHF® 4 port

Package content

- Antenna cable
- Nut, toothed washer

Images



Interface

Connector 1:	1 x RP-SMA jack bulkhead
Connector 2:	1 x I-PEX Inc., MHF® 4 plug

Technical characteristics

Impedance:	50 Ω
------------	------

Physical characteristics

Thread length:	9 mm
Cable category:	coaxial
Cable type:	0.81
Cable attenuation:	4.9 dB @ 2.40 GHz per meter
Cable colour:	black
Cable length incl. connectors:	20 cm
Smallest bending radius:	3.24 mm
Diameter mounting hole:	6.5 mm
Cable diameter:	0.81 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

