

# Gigabit Ethernet Switch 4 Port + 1 SFP

## Description

This Gigabit Ethernet Switch by Delock can be used to connect different network components. In addition, the built-in SFP slot allows you to expand the network with a fiber optic connection.



**Item no. 87704**

EAN: 4043619877041

Country of origin: China

Package: White Box

## Technical details

- Connector:
  - 4 x RJ45 jack for 10/100/1000 Mb/s Base-T
  - 1 x SFP slot for 1 Gb/s SFP module (SFP module not included)
  - 1 x IEC C14 connector
- Data transfer rate up to 1 Gb/s
- Supports IEEE 802.3 / 802.3u / 802.3z / 802.3ab
- LEDs for status monitoring
- VLAN (port isolation or 1:1 mode) selectable by DIP switch
- 330 m long range mode with 10 Mb/s
- Robust metal housing
- Removable wallmount brackets
- Fanless
- Internal power supply
- Power consumption: max. 10 W
- Operating temperature: -20 °C ~ 60 °C
- Dimensions (LxWxH): ca. 125 x 109 x 32 mm

## System requirements

- Device with one free RJ45 port

---

## Package content

- Switch
- Wall mounting brackets
- 4 x screw
- Power cord
- User manual

---

## Images



## General

Mounting type:	wall
----------------	------

## Interface

Output:	4 x RJ45 jack
Input:	1 x SFP jack 1 x IEC C14 connector

## Technical characteristics

Data transfer rate:	Gigabit Ethernet up to 1 Gbps
Operating temperature:	-20 °C ~ 60 °C

## Physical characteristics

Housing colour:	black
Housing material:	metal
Length:	125 mm
Width:	109 mm
Height:	32 mm

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de