

Eaton 16NHG000B

Catalog Number: 16NHG000B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 16A, 120 kAIC, Combination fuse status indicator, fuse, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Ceramic body

General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	16NHG000B
	Packing Unit
	Pack
	Case Pack
EAN	Quantity
5027590190985	3
5027590363570	60
Gross Weight	Length
0.392 kg	83 mm
8.205 kg	420 mm
Width	Height
78 mm	56 mm
180 mm	140 mm
Volume	ERP Name
362.544 cm ³	SAP-UNITY
10584 cm ³	SAP-UNITY
Product Length/Depth	Product Height
79 mm	51 mm
Product Width	Product Weight
21 mm	119.333 g

Compliances

CE Marked

Certifications

IEC 60269-1

Electrical data

Amperage Rating

16 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Model Code

NH FUSE 16A 500V SIZE 000 GGL

Fuse size

NH000

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

Microswitch 170H0236

EBF Vertical fuse rail

EBV Vertical fuse switch-disconnectors

EBH Size 000 Horizontal fuse switch-disconnectors

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia