

Cable DVI 12+5 male to VGA male 5 m

Description

This DVI to VGA cable by Delock supports the transfer of analog video signals and can be used to connect a VGA monitor or a projector to the DVI interface of a PC or laptop.



Item no. 86751

EAN: 4043619867516

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x DVI 12+5 male >
 - 1 x VGA male
- DVI and VGA connectors with screws
- Cable gauge: 30 AWG
- Cable diameter: ca. 8 mm
- Copper conductor
- Contacts gold-plated
- Cable double shielded
- Resolution up to 1920 x 1200 @ 60 Hz
(depending on the system and the connected hardware)
- Colour: black
- Length incl. connectors: ca. 5 m

System requirements

- PC or laptop with a free DVI port

Package content

- DVI to VGA cable

Images



General

Specification:	DVI-A (Single Link)
----------------	---------------------

Interface

Connector 1:	1 x DVI 12+5 male
Connector 2:	1 x VGA male

Technical characteristics

Data transfer rate:	3.96 Gbps
Maximum screen resolution:	1920 x 1200 @ 60 Hz

Physical characteristics

Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	30 AWG
Shielding:	double
Length:	5 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de