

**Product Name // MP22SLPINRB220A5 Power Symbol
 Illumination Vandal Resistant Switch**
 [View Product Page](#)

// Product Description:

- | | |
|-----------------------------|------------------|
| ⬡ MP22 Range | ⬡ Blue |
| ⬡ SPDT | ⬡ 220V |
| ⬡ Latching | ⬡ AL alloy Black |
| ⬡ Power Symbol Illumination | ⬡ IP65 |

// General Information:

| | |
|----------------------------------|---|
| Product Display Title: | Power Symbol Illumination Vandal Resistant Switch |
| Product Family: | Switch Range |
| Product Series: | Vandal Resistant Switches |
| Bezel Finish: | Gloss |
| Body Colour: | Black |
| Body Material: | Aluminium |
| Body Material Type: | Metal |
| Current Rating: | 5A 250V |
| Diameter: | 22mm |
| Dielectric Withstanding Voltage: | 1500V |
| Durability: | 50,000 |
| Function: | Push Button Switch |
| Illumination Colour: | Blue |
| Illumination Shape: | Power Symbol |
| Illumination Voltage: | 220V |
| Ip Rating: | IP65 |
| Lamp Type: | LED |
| Material Finish: | Gloss |
| Max Operating Temperature: | 55°C |
| Min Operating Temperature: | -25°C |
| Max Panel Thickness: | 8mm |
| Operating Humidity: | 45~85 RH(Non condensing) |
| Panel Cut Out: | 22mm Diameter circle |
| Rohs Compliant: | Yes |
| Switch Body Colour: | Black |
| Switch Body Material: | Aluminium |
| Switch Button Colour: | Black |
| Switch Button Material: | Aluminium |
| Switch Circuit: | SPDT |
| Switch Series: | MP22 |
| Switch Shape: | Round |
| Switch Type: | Pushbutton |
| Switching Type: | Latching |
| Thread Size: | M22 |

// Product PDF Links
 [22mm Vandal Resistant Switch](#)
// Product 3D CAD Model Links
 [MP22SLPINRB220A53D CAD Model](#)