

# USB 10 Gbps Cable USB Type-C™ male to male PD 3.0 100 W E-Marker 1 m red metal

## Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB Type-C™ port. The integrated E-Marker chipset supports the PD 3.0 function for fast charging with a charging power of up to 100 W.

### Metal housing and strain relief

Thanks to the elegant metal housing and sturdy strain relief on both sides, the cable is optimally protected against damage in everyday use.



1 m

**Item no. 80098**

EAN: 4043619800988

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:  
2 x USB 10 Gbps USB Type-C™ male
- Chipset: E-Marker
- Connector with metal housing
- Cable gauge:  
30 + 32 AWG data line  
22 AWG power line
- Cable diameter: ca. 5.5 mm
- Contacts gold-plated
- Connectors gold-plated
- Cable triple shielded
- Data transfer rate up to 10 Gbps
- USB Power Delivery (USB PD 3.0) support up to 100 watt (20 V / 5 A)
- Colour: black / red
- Length incl. connectors: ca. 1 m

## Package content

- USB cable

---

## Images



## General

Specification:	USB 10 Gbps
Style:	both sides identical

## Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x USB Type-C™ male

## Technical characteristics

Chipset:	E-Marker
Data transfer rate:	10 Gbps
Maximum power:	100 W
Maximum current:	5 A
Voltage:	20.0 V

## Physical characteristics

Connector finishing:	gold-plated
Pin finishing:	gold-plated
Cable gauge:	30 AWG data line 32 AWG data line 22 AWG power line
Shielding:	triple
Length:	1 m
Colour:	red black
Cable diameter:	5.5 mm

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin

Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de