

4 Port USB 2.0 Cable Hub with USB Type-C™ connector 60 cm

Description

This USB hub by Delock can be connected to a computer, laptop or mobile device via the **USB-C™** interface. It expands the computer by **4 USB Type-A ports**. Different USB devices such as USB flash memory, card reader, external enclosure etc. can be connected.

Flexible cable

The hub can be flexibly used by its cable and various USB devices can be connected.

The cable is very sturdy and durable due to its **robust textile shielding, strong strain relief** and **metal housing** at all cable ends.



Item no. 64210

EAN: 4043619642106

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
1 x USB 2.0 USB Type-C™ male
4 x USB 2.0 Type-A female
- Data transfer rate up to 480 Mbps
- Maximum output current: 1.5 A
- Cable with textile shielding
- Connector with metal housing
- Cable length incl. connectors: ca. 60 cm
- Colour: black / grey
- Plug & Play

System requirements

- Android 11.0 or above
- Chrome OS
- Linux Kernel 5.15 or above
- Mac OS 13.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7

- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

Package content

- Hub
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Android 11.0 or above Linux Kernel 5.15 or above Mac OS 13.1 or above

Interface

Connector 1:	1 x USB 2.0 USB Type-C™ male
Connector 2:	4 x USB 2.0 Type-A female

Technical characteristics

Data transfer rate:	480 Mbps
---------------------	----------

Physical characteristics

Cable length incl. connectors:	60 cm
--------------------------------	-------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de