

RS-232 Cable Serial D-Sub 9 female to female null modem with narrow plug housing - Full Handshaking - 5 m

Description

This serial cable by Delock is a **full handshake null modem cable** with RTS / CTS and DTR / DTS data flow control. This cable offers the possibility to connect RS-232 devices directly with each other. Optionally, devices can be supplied with power via the RI line.

Mini D-Sub 9 connector

These cables fit any RS-232 port, as the **mini D-Sub 9 connectors** (44 x 33.3 x 15 mm) are small and compact. In this way, RS-232 connections can be used next to each other.



5 m

Item no. 87516

EAN: 4043619875160

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x serial D-Sub 9 female with screws >
 - 1 x serial D-Sub 9 female with screws
- Cable gauge: 28 AWG
- Full handshaking cable
- Pin assignment: 2 – 3, 3 – 2, 4 – 6, 6 – 4, 5 – 5, 7 – 8, 8 – 7, 9 – 9, shielded
- Colour: black
- Insulator: PVC
- Screw type: #4-40 UNC
- Cable diameter: ca. 5 mm
- Cable length incl. connectors: ca. 5 m


System requirements

- A free D-Sub 9 male port

Package content

- Cable

Images



General

Specification:	RS-232 (EIA / TIA)
Style:	Mini Sub-D9 Nullmodem "Full Handshaking" both sides identical

Interface

Connector 1:	1 x serial D-Sub 9 female with screws
Connector 2:	1 x serial Sub-D 9 female with screws

Technical characteristics

Data transfer rate:	921.6 Kbps
Signal transmission:	TxD, RxD, RTS, CTS, DTR, DSR, RI, GND + Schirmung

Physical characteristics

Cable type:	AWM Style 2464 28 AWG 80 °C 300 V VW-1
Cable length incl. connectors:	5 m
Pin finishing:	gold-plated
Conductor material:	Copper tinned
Cable gauge:	28 AWG
Screw type:	#4-40 UNC
Colour:	black
Cable diameter:	5 mm
Cable jacket material:	PVC
Safety of Flammability:	VW-1

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	info@delock.de
Website	www.delock.de