

MUSW-4B-01

Wireless optical mouse, black

COMFORT AND PRECISION

- Intelligent power saving technology Long battery life
- No mouse pad required



Features

- 4-button wireless optical mouse with USB Nano-receiver CPI button for quick resolution changes (800 1600 DPI)

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

60
0.076995
6.36
175x125x60 mm
590x435x300 mm
CN
8716309103855
8522900090

Package contents

Mouse USB nano receiver

Specifications

Wireless technology: 2.4 GHz, GFSK RF modulation, 80 channels, 32 bit device ID

Operating distance: up to 10 m

Power class: RF power 3 dBm (max. EIRP)

Internal antenna type; antenna gain in dBi (typical): 2 dBi ±1 dBi

Optical resolution: 800, 1200, 1600 DPI selectable by the button

Power supply: AA battery x 1 pcs (not included)

Power consumption: 1.5 V DC, up to 15 mA

Nano receiver: USB 1.1 compatible, weight 2 g, 6 x 14 x 18 mm

System requirements

Windows 7/8/10

Free USB port for the receiver

Certificates

