

USB Type-A Network Adapter 5 Gigabit LAN 1 x RJ45

High speed: Data transfer rates up to 5 Gbps

This USB network adapter by Delock offers a reliable and fast network connection. With a transmission speed of up to 5 gigabits per second, it enables efficient working and smooth streaming.

Compact and lightweight design

The compact and lightweight design makes the adapter ideal for use on the go or in the office. It also ensures a stable and secure network connection with consistent performance. The adapter is compatible with Windows, Mac OS and Linux, making it very versatile.

NBASE-T for higher speed

Modern services and new technologies require higher bandwidths. NBASE-T technology enables speeds of 1 Gbps, 2,5 Gbps and 5 Gbps with conventional networking cables. The best possible transmission rate is set automatically.



Item no. 81571

EAN: 4043619815715

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 10 Gbps Type-A male
 - 1 x 5 Gigabit LAN RJ45 jack
- Chipset: Realtek RTL8157
- Data transfer rate:
 - Ethernet up to 10 Mbps
 - Fast Ethernet up to 100 Mbps
 - Gigabit Ethernet up to 1000 Mbps
 - NBASE-T with up to 2.5 Gbps and 5 Gbps
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure
- Supports 16k Jumbo Frames
- LED indicator for link and activity
- USB bus powered
- Robust metal housing
- Colour: anthracite
- Cable length without connectors: ca. 15 cm
- Dimensions (LxWxH): ca. 60 x 27 x 16 mm

System requirements

- Linux Kernel 6.5 or above
- Mac OS 14.5 or above
- Windows 10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- USB Type-A 5 Gigabit LAN adapter
- User manual

Images



General

Specification:	USB 10 Gbps
Supported operating system:	Windows 10 32-Bit Windows 10 64-Bit Windows 11 Linux Kernel 6.5 or above Mac OS 14.5 or above
LED indicator:	Link and activity

Interface

Connector 1:	1 x USB 10 Gbps Type-A male
Connector 2:	1 x Gigabit LAN RJ45 jack

Technical characteristics

Chipset:	Realtek RTL8157
Data transfer rate:	Ethernet up to 10 Mbps Fast Ethernet up to 100 Mbps Gigabit Ethernet up to 1 Gbps Gigabit Ethernet up to 2.5 Gbps Gigabit Ethernet up to 5 Gbps

Physical characteristics

Housing material:	Aluminium
Cable length:	15 cm
Length:	60 mm
Width:	27 mm
Height:	16 mm
Colour:	anthracite

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167

City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de