

WiFi 5.8 GHz Antenna RP-SMA plug 3 dBi omnidirectional with connection cable RG-174 3 m black self-adhesive

Description

This WiFi 5.8 GHz antenna by Delock allows the usage of WiFi frequency range 5.15 GHz to 5.85 GHz indoors.



Item no. 10035

EAN: 4043619100354

Country of origin: China

Package: Box

Technical details

- Connector: 1 x RP-SMA plug
- Frequency range: 5.15 GHz - 5.85 GHz
- Antenna gain: 3 dBi
- Impedance: 50 Ohm
- VSWR: 1.5:1
- Cable type: RG-174
- Cable attenuation: 0.9 dB @ 800 MHz per meter
- Cable colour: black
- Cable length: ca. 3 m
- Polarisation: linear, vertical
- Operating temperature: -40 °C ~ 70 °C
- Housing material: ABS
- Colour: black
- Dimensions (LxWxH): ca. 115 x 22 x 5 mm

System requirements

- Device with a free RP-SMA jack

Package content

- Antenna

General

Mounting type:	self adhesive
Suitable for indoor:	yes

Interface

Connector:	1 x RP-SMA plug
------------	-----------------

Technical characteristics

Frequency range:	5150 - 5850 MHz
Antenna gain:	3 dBi
Impedance:	50 Ω
Polarisation:	linear vertical
VSWR:	1.5

Physical characteristics

Housing material:	ABS
Cable category:	coaxial
Cable attenuation:	0.9 dB @ 800 MHz per meter
Cable colour:	black
Cable length incl. connectors:	3 m
Length:	115 mm
Width:	22 mm
Height:	5 mm
Colour:	black
Cable diameter:	2.7 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167

City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

