

Cable Mini DisplayPort 1.2 male > Mini DisplayPort male 4K 60 Hz 1 m

Description

This Mini DisplayPort cable by Delock can be used to connect devices with Mini DisplayPort interface, e.g. displays, projectors or TVs, to a PC or laptop. The triple shielded cable supports a resolution of up to Ultra HD (4K @ 60 Hz) and is downwards compatible to Full-HD 1080p.



Item no. 83473

EAN: 4043619834730

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x mini DisplayPort male >
 - 1 x mini DisplayPort male
- DisplayPort 1.2 specification
- Pin 20 not connected
- Cable gauge: 32 AWG
- Cable diameter: ca. 5.5 mm
- Copper conductor
- Net shielding
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 21.6 Gb/s
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Colour: black
- Cable length: ca. 1 m

System requirements

- One free mini DisplayPort female

Package content

- Mini DisplayPort cable

Images



General

Specification:	DisplayPort 1.2
Style:	both sides identical

Interface

Connector 1:	1 x mini DisplayPort male
Connector 2:	1 x mini DisplayPort male

Technical characteristics

Data transfer rate:	21.6 Gbps
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Connector finishing:	gold-plated
Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	32 AWG
Shielding:	triple
Length:	1 m
Colour:	black
Cable diameter:	5.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de