

Metallic conduits with liquid-tight cover

- LTSUL, Galvanised Steel Conduit, PVC Cover, UL Listed

Machine tools or outdoor installations, liquid-tight applications where UL listing is required.

Features and Benefits


- Liquid-tight (IP68 and IP69k with LTS fittings)
- UL-listed and CSA approved
- High compression, tensile and impact strength
- Good flexibility
- Smooth outer cover does not wrinkle when bent
- Good resistance to acids, petrol, oils and greases
- UV-resistant, suitable for outdoor use
- Colour: black



HelaGuard LTSUL.



The HelaGuard LTSUL galvanised steel conduit with a PVC Cover is UL listed and typically used on drilling platforms.



HelaGuard liquid-tight metallic conduit, plastic coating

MATERIAL	Galvanised Steel (GS), Polyvinylchloride (PVC), Copper (CU)
Operating Temperature	-15 °C to +75 °C
Specifications	CSA, UL: Listed



TYPE	Nominal Ø	US Trade Size	Outside Ø (OD)	Inside Ø (ID)	Min. Bending Radius (R)	Weight (g/m)	Reel Length	Colour	Article-No.
LTSUL16	16	3/8 "	17.8	12.6	50	432	25 m	Black (BK)	166-32100
LTSUL20	20	1/2 "	21.1	16.0	90	477	25 m	Black (BK)	166-32101
LTSUL25	25	3/4 "	26.4	21.1	110	789	25 m	Black (BK)	166-32102
LTSUL32	32	1 "	33.1	26.5	140	1,221	15 m	Black (BK)	166-32103
LTSUL40	40	1 1/4 "	41.8	35.4	180	1,519	15 m	Black (BK)	166-32104
LTSUL50	50	1 1/2 "	47.9	40.4	230	1,846	15 m	Black (BK)	166-32105
LTSUL63	63	2 "	59.7	51.6	280	2,159	15 m	Black (BK)	166-32106

All dimensions in mm. Subject to technical changes. Other reel lengths available on request. Minimum Order Quantity (MOQ) may differ from package content.



Please note! Not all products listed on this page may have this approval.