

USB Type-C™ Adapter to Gigabit LAN with Power Delivery port grey

Description

The adapter by Delock expands a PC or laptop by one network interface via the USB Type-C™ interface. In addition, the adapter can also be operated on a **Thunderbolt™ 3 interface**.

USB Power Delivery (USB PD 3.0) support up to 100 watt

The adapter has a **USB Type-C™ Power Delivery port** to connect the power supply of the laptop or tablet to charge it.

Small sturdy helper

Due to its small dimensions and its **sturdy housing**, this Delock adapter is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.

Please Note

When using with MacBook, the driver has to be installed first.



Item no. 64116

EAN: 4043619641161

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ male >
 - 1 x Gigabit LAN RJ45 jack
 - 1 x USB Type-C™ PD female (power supply)
- Chipset: ASIX AX88179
- SuperSpeed USB - 5 Gbps specification
- Data transfer rate:
 - Ethernet up to 10 Mbps (Half/Full Duplex)
 - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
 - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
- Compatible with:
 - IEEE 802.3: 10BASE-T
 - IEEE 802.3u: 100BASE-TX
 - IEEE 802.3ab: 1000BASE-T
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports Wake On LAN (WOL)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure flow control

- Supports 4k Jumbo Frames
- Output power for host: max. 100 W
- Housing material: aluminium / plastic
- LED indicator for power and activity
- USB bus powered
- Colour: grey
- Cable length incl. connectors: ca. 15.5 cm
- Dimensions (LxWxH): ca. 56 x 23.5 x 23.5 mm

System requirements

- Android 10.0 or above
- Chrome OS
- Linux Kernel 5.4 or above
- Mac OS 10.15.6 or above
- Windows 8.1/8.1-64/10/10-64/11
- Laptop or tablet with a free USB Type-C™ or Thunderbolt™ 3 port

Package content

- USB Type-C™ Gigabit LAN adapter
- User manual

Images



General

Supported operating system:	Chrome OS Linux Kernel 5.4 or above Mac OS 10.15.6 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018) Android 10.0 or above
LED indicator:	1 x

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	1 x Gigabit LAN RJ45 jack
Connector 3:	1 x USB Type-C™ Power Delivery female

Technical characteristics

Chipset:	ASIX AX88179
Data transfer rate:	Ethernet up to 10 Mbps Fast Ethernet up to 100 Mbps Gigabit Ethernet up to 1000 Mbps

Physical characteristics

Colour:	grey
---------	------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de