

1385
Młotki miedziane

	art.	 g	A mm	L mm	L1 mm
013850404	1385 400	400	26	260	75
013850406	1385 600	600	32	270	80
013850408	1385 800	800	34	280	90
013850410	1385 1000	1000	37	280	100
013850415	1385 1500	1500	43	280	110
013850420	1385 2000	2000	48	300	120

