

USB 2.0 Type-C™ Network Adapter 10/100 Mbps LAN 1 x RJ45

Description

The adapter by Delock expands a PC or laptop by one network interface via the USB Type-C™ interface. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.



Item no. 64306

EAN: 4043619643066

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
1 x USB 2.0 Type-C™ male
1 x LAN RJ45 jack
- Chipset: Realtek RTL8152
- Data transfer rate:
Ethernet up to 10 Mbps (Half/Full Duplex)
Fast Ethernet up to 100 Mbps (Half/Full Duplex)
- Compatible with:
IEEE 802.3: 10BASE-T
IEEE 802.3u: 100BASE-TX
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Current consumption: ca. 150 mA
- USB bus powered
- Colour: black
- Cable length without connectors: ca. 11 cm
- Dimensions (LxWxH): ca. 60 x 27 x 16 mm

System requirements

- Mac OS 10.10 or above
- Windows 10/10-64/11

- PC or laptop with a free USB Type-C™ or Thunderbolt™ 3 port
-

Package content

- USB 2.0 LAN adapter
 - User manual
-

Images



General

Specification:	USB 2.0
Supported operating system:	Mac OS 10.10 or above Windows 10 32-Bit Windows 10 64-Bit Windows 11

Interface

Connector 1:	1 x USB 2.0 USB Type-C™ male
Connector 2:	1 x RJ45 jack

Technical characteristics

Chipset:	Realtek RTL8152
Data transfer rate:	Ethernet up to 10 Mbps Fast Ethernet up to 100 Mbps

Physical characteristics

Housing colour:	black
Length:	60 mm
Width:	27 mm
Height:	16 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de