

USB 5 Gbps Active Cable USB Type-A to USB Type-B 20 m

Description

This active USB cable by Delock with integrated signal amplifiers is used to connect devices with USB Type-B female port to a PC or laptop with USB Type-A port.

To ensure reliable data and power transmission, the included power supply unit must be connected to the cable via the DC socket on one of the signal amplifiers.



Item no. 85382

EAN: 4043619853823

Country of origin: China

Package: White Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-A male
 - 1 x USB 5 Gbps Type-B male
 - 1 x DC jack
- Chipset: Genesys Logic GL3523
- Status LED
- Cable gauge:
 - 28 AWG data line
 - 24 AWG power line
- Cable diameter: ca. 5.5 mm
- Data transfer rate up to 5 Gbps
- Colour: black
- With 4 signal amplifiers (at intervals of 5 m)
- Dimensions of signal amplifier (LxWxH): ca. 6.7 x 2.2 x 1.2 cm
- Length incl. connectors: ca. 20 m

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.25 A
- Output: 5 V / 1 A

- Ground outside, plus inside
- Dimensions:
 - inside: $\varnothing$ ca. 1.1 mm
 - outside: $\varnothing$ ca. 3.5 mm
 - length: ca. 7.0 mm

System requirements

- PC or laptop with a free USB Type-A port

Package content

- USB 5 Gbps cable
- External power supply

Images



General

Specification:	USB 5 Gbps
----------------	------------

Interface

Connector 1:	1 x USB 5 Gbps Type-A male
Connector 2:	1 x USB 5 Gbps Type-B male

Technical characteristics

Chipset:	Genesys Logic GL3523
Data transfer rate:	5 Gbps

Physical characteristics

Cable gauge:	28 AWG data line 24 AWG power line
Length:	20 m
Colour:	black
Cable diameter:	5.5 mm

Power supply

Power supply type:	Euro wall power supply
Input voltage:	AC 100 - 240 V / 50 - 60 Hz / 0.25 A
Power supply output:	5.0 V / 1.0 A
Power supply connector:	DC male 3,5 mm x 1,1 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de