




MATERIAL: BRASS
 THICKNESS: 0.25
 HARDNESS: SH
 PLATING: TIN 40 μ MIN
 WIRE RANGE: (AWG) 18-24
 INSULATION O.D.: 3.8 MAX.
 VOLTAGE RATING: AC/250V, DC/350V
 CURRENT RATING: AC, DC, 10A
 TEMPERATURE RANGE: -25°C TO +85°C

DIMENSION: (MM)

T: 0.25 $\pm$ 0.03
 L: 20.5 $\pm$ 0.35
 E: 13.3 $\pm$ 0.25
 W: 3.6 $\pm$ 0.25
 W1: 4.2 $\pm$ 0.25
 IS: 3.8 $\pm$ 0.3
 WS: 2.6 $\pm$ 0.3
 H: 3.5 $\pm$ 0.3
 H1: 2.1 $\pm$ 0.3
 D: 3.2 $^{+0.1}_{-0.25}$
 D1: 2.0 $\pm$ 0.06
 e: 8.6 $\pm$ 0.3

RoHS
Compliant

Ninigi


APPD.
核准

DWG.
製圖

DATE 制表日

2009/07/16

Hedy



SCALE
比例 參考

UNIT
單位 MM

PAGE
張數 1 / 1

TOLERANCE
容許公差

0 $\pm$
0.00 $\pm$
ANG. $\pm$

SIZE
紙張尺寸 A 4

REV.
版次 A

PART NAME 品名

JST 2.0mm FEMALE TERIMNAL
 BRASS MATERIAL TIN PLATING
 AWG18~24 1ROLL=5000PCS ROHS LOW-LEAD

PART NO.

料號

TAMIYA-FT2