




	Art.	M mm	L mm	L1 mm	Ø mm	A mm	A1 mm	g
009490008	949 8	8	220	160	12,4	7	50	140
009490010	949 10	10	230	160	14,9	8,5	50	170
009490012	949 12	12	240	175	17,5	9,5	50	225
009490013	949 13	13	244	175	18,7	10,5	55	235
009490014	949 14	14	250	190	20,1	11,5	55	290
009490017	949 17	17	264	200	23,8	13	60	440



Scan the QR Code to access the web tab

Specs, media and documentation in one click.

