



BETA 7272V
FitEVOLUTION woven fabric shoe, hard-wearing and highly breathable



Certifications and Standards

CE S1PS FO SR ESD EN ISO 20345:2022

Features

Flyknit upper provides comfort and breathability, while neon green details add a touch of style.

FIT4YOU system

Create your own comfort with BETA's patented FIT4YOU system: a special cavity in the penetration proof insole allows you to replace the ETPU insole at any time, choosing from three different densities included in the pack.

ETPU inserts

ETPU is known for its excellent anti-shock and shock-absorbing properties. The three inserts soft, intermediate and rigid make it easy and immediate to customise the softness and support of the shoe to suit your needs.

Breathable and resistant

The durable woven fabric upper is incredibly lightweight thanks to the open weave that promotes air circulation. It is also surprisingly durable, ideal for shoes built to last, without compromising on quality.

Metal-free

Composite toe cap and midsole are made of composite material to provide lightweight, metal-free protection.



FIT4YOU
 Patented FIT4YOU technology allows customisation of shoe cushioning.



Customised comfort
 The special pressed sheet allows you to create your own comfort by choosing from 3 different ETPU inserts included in the pack.



ESD protection
 ESD certified to protect user and machinery from electrostatic charges.



Certifications and Standards

CE S1PS FO SR ESD EN ISO 20345:2022



Specifications

LACING:	traditional
WEIGHT (INDICATIVE SIZE 42):	550 g
TYPE:	low

Lightness

- Hard-wearing, highly breathable woven fabric with TPU (thermoplastic polyurethane) inserts
- Heel stability support
- Traditional lacing

Comfort

Dual-density polyurethane

Safety



3-density cushioning ETPU insert and EVA FOAM underfoot cover

Protections

Tip: Polymer material, 200 joules.

Durability: Composite fibre, ceramic treatment.

Coded items

	Art.	EU	UK	 mm
072720137	7272V 37	37	4,5	251
072720138	7272V 38	38	5	257
072720139	7272V 39	39	6	263
072720140	7272V 40	40	6,5	269
072720141	7272V 41	41	7	276
072720142	7272V 42	42	8	282
072720143	7272V 43	43	9	290
072720144	7272V 44	44	10	296
072720145	7272V 45	45	10,5	304
072720146	7272V 46	46	11	311
072720147	7272V 47	47	12	317
072720148	7272V 48	48	13	324

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

