



BETA 666/C5

Zero-Reset click-type torque wrench, in case, with sockets and extension bars



Certifications and Standards



UNI EN ISO 6789

Features

Designed for precision maintenance and assembly, the 666/C5 kit ensures flawless results and operational safety in every use.

GREATER ORGANISATION

The robust drawer ensures that your tools are always tidy and protected.

VERSATILITY OF APPLICATION

In addition to the torque wrench, sockets, extensions and related fittings are also included in the cassette for more efficient, faster and more versatile work.



REVERSIBLE RATCHETS

72-tooth mechanism for fast and precise use of the wrench, ensuring a recovery angle of only 5°.



DOUBLE GRADUATED SCALE

High scale visibility. Easily selectable setting with extremely precise increment.



BIMATERIAL HANDLE

The ergonomic handle provides a comfortable and secure grip. Made of materials resistant to fuels, oils and industrial liquids

Certifications and Standards



UNI EN ISO 6789

666/5: n. ZERO-RESET click-type torque wrenches □ 10÷50 Nm
 910A: n. 3/8" hexagon hand sockets □ 8÷19 mm
 910/21 - 910/22: n. 3/8" extension bar 125-250 mm
 910/15: n. 0 adaptor, 3/8" female and 1/4" male drivers E 3/8 - B 1/4
 910/16: n. 0 adaptor, 1/2" female and 3/8" male drives E 3/8 - B 1/2
 895/3: n. 0 socket holder

Coded items

	Art.
006661005	666/C5

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

