

KVM 4 in 1 Multiview Switch 4 x HDMI with USB 2.0

Description

This KVM switch by Delock is a convenient solution for connecting **four computers** with HDMI output **to one HDMI monitor**. Furthermore, four **USB 2.0** Type-A ports can be used to connect a mouse, keyboard, printer or USB drive.

4 in 1 Multiview Mode

In Multiview Mode, **all 4 PCs are displayed on one monitor simultaneously**. Operating the keyboard and mouse is possible without switching. When the **mouse** is moved over one of the desktops, it is **activated for input**. Alternatively, the Sync Mode can be turned on, where all connected PCs receive the same signals from the input devices.

Flexible Control

The active computer can be selected by mouse button, keyboard hotkey, button on the device or infrared remote control.

Please Note

KVMs emulate a standard wired 104 key keyboard and wired generic 2 or 3 button scroll wheel mouse on their respective console ports. Whether or not a wireless or gaming mouse and keyboard work with KVM switches depends on several factors; in general, most wireless mice and keyboards do not support working with KVM switches. We recommend to use a standard wired mouse and keyboard with our KVM switches.



Item no. 11488

EAN: 4043619114887

Country of origin: China

Package: White Box

Technical details

- Connectors:
Input:
4 x HDMI-A female
4 x USB 2.0 Type-B female
1 x 12 V DC jack
Output:
1 x HDMI-A female
4 x USB 2.0 Type-A female
- 2 switch buttons with LED indicator for source (PC1 - PC4) and audio

- Switching via button, mouse button, hotkey or infrared remote control
 - High Speed HDMI specification
 - Supports HDCP 1.2
 - Resolution (HDMI input) up to 1920 x 1080 @ 60 Hz
(depending on the system and the connected hardware)
 - Resolution (HDMI output) 1280 x 720 or 1920 x 1080 @ 50 or 60 Hz
 - Video bandwidth up to 225 MHz / 2.25 Gbps
 - USB 2.0 up to 480 Mbps
 - Robust metal housing
 - Colour: black
 - Dimensions (LxWxH): ca. 210 x 160 x 44 mm
-

Power supply specification

- Wall power supply
 - Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.8 A
 - Output: 12.0 V / 2.0 A
 - Ground outside, plus inside
 - Dimensions:
 - inside: ø ca. 2.1 mm
 - outside: ø ca. 5.5 mm
 - length: ca. 10 mm
-

System requirements

- PC with HDMI female + USB Type-A female
 - Monitor or TV with HDMI connector
-

Package content

- KVM switch
- Remote control
- External power supply
- Mounting brackets and screws
- User manual

Images



General

Specification:	HDMI 1.3 USB 2.0
----------------	---------------------

Interface

Output:	4 x USB 2.0 Type-A female 1 x HDMI-A female
Input:	4 x USB 2.0 Type-B female 4 x HDMI-A female 1 x DC 5.5 x 2.1 mm female

Technical characteristics

Data transfer rate:	USB 2.0 up to 480 Mb/s
Maximum screen resolution:	1920 x 1080 @ 60 Hz

Physical characteristics

Housing colour:	black
Housing material:	metal
Length:	210 mm
Width:	160 mm
Height:	44 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de