



BETA 7343N
RENEGADE microfibre ankle shoe, water-repellent



Certifications and Standards

CE S3S FO SR HRO EN ISO 20345:2022

Features

The 7343N safety footwear focuses on comfort, style and durability, providing comfort and style throughout the working day

SAFETY WITH STYLE

The shoe that offers protection without sacrificing looks. Thanks to the "urban" style, inspired by sports shoes, it is also perfect to wear after work.

EXTREME COMFORT

Renegade combines advanced cushioning and superior support to provide exceptional comfort throughout the working day. Thanks to its innovative design and high performance, it ensures a smooth and comfortable walk.

WIDE FOOTBED

The wide fit further enhances the comfort of the shoe, preventing possible constriction of the foot at any time of day.

ALL-SEASON DURABILITY

The water-repellent microfibre upper is distinguished by its outstanding resistance to stains and scratches, making it particularly suitable for year-round use. It is the ideal solution for shoes designed to last, without compromising on quality.



INNOVATIVE DESIGN

The 7343N shoe combines sporty design and modern style, highlighting an innovative outsole that ensures safety and comfort with every step



TRADITIONAL LACING

The possibility of tightening or loosening the laces allows for a secure and customised fit



MAXIMUM RESISTANCE

The rubber outsole makes the shoe extremely durable and heat-resistant up to 300°C.



Certifications and Standards



Specifications

LACING: traditional
 WEIGHT (INDICATIVE SIZE 42): 510 g
 TYPE: high

Lightness

- Water-repellent microfibre with TPU (thermoplastic polyurethane) inserts
- Heel stability support
- Traditional lacing

Comfort

- EVA (ethylene vinyl acetate) midsole
- Durable nitrile rubber tread

Safety

EVA FOAM underfoot cover

Protections

Tip: Polymer material, 200 joules
 Durability: Composite fibre, ceramic treatment

Coded items

	Art.	EU	UK	 mm
073430537	7343N 37	37	4,5	248
073430538	7343N 38	38	5	254
073430539	7343N 39	39	6	261
073430540	7343N 40	40	6,5	268
073430541	7343N 41	41	7	274
073430542	7343N 42	42	8	281
073430543	7343N 43	43	9	288
073430544	7343N 44	44	10	294
073430545	7343N 45	45	10,5	301
073430546	7343N 46	46	11	308
073430547	7343N 47	47	12	314
073430548	7343N 48	48	13	321

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

