

Wireless Car Charger Smartphone Holder with Charging and Cooling Function 15 W – Qi

Description

With this **Qi certified holder** by Delock a mobile device can be **charged wirelessly in the car**. With the energy transfer by induction, charging cables are no longer needed and the connectors are protected. The charger supports fast charging **up to 15 watts** for suitably equipped smartphones.

Active cooling

The **cooling** of the holder ensures that the mobile phone does not overheat and switch off even during prolonged use, such as navigation.

Smart touch buttons

Once the phone is placed in the holder, the fastening arms close automatically and hold the mobile device in place. To release it, there are two buttons on the side which are also used to extend or retract the mounting arms using a motor. The lower holder can be extended manually so that larger phones can also be accommodated.



Item no. 66939

EAN: 4043619669394

Country of origin: China

Package: Retail Box

Technical details

- Connector: 1 x USB Type-C™ female
- Input voltage: 12.0 V / 2.0 A
- Charging power: 5.0 V / 1.0 A (5.0 W), 7.5 V / 1.0 A (7.5 W), 9.0 V / 1.12 A (10.0 W), 12.0 V / 1.25 A (15.0 W)
- Frequency range: 110 - 205 kHz
- Transmission power: max. 15 W
- 1 x LED for power
- Operating temperature: -10 °C ~ 40 °C
- Storage temperature: -20 °C ~ 40 °C
- Relative humidity: 5 - 95 % (non condensing)
- Transmission distance: 3.5 mm
- With suction cup holder
- Ventilation slot clip
- FOD (Foreign Object Detection): yes
- Colour: black / grey
- Suitable for mobile devices up to ca. 90 mm width
- Weight: ca. 174 g
- Dimensions (LxWxH): ca. 130 x 100 x 75 mm

Package content

- Holder
- Telescopic arm with suction cup
- Ventilation slot clip
- 2 x Fastening nut
- Charging cable USB Type-A male to USB-C™ male, length ca. 1 m
- User manual

Images



General

LED indicator:	Power
----------------	-------

Interface

Connector 1:	1 x USB Type-C™ female
--------------	------------------------

Technical characteristics

Frequency range:	110 - 205 kHz
Voltage supply:	12.0 V / 2.0 A input voltage

Physical characteristics

Weight:	174 g
Length:	130 mm
Width:	100 mm
Height:	75 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

