

19" Patch Panel 24 Port Cat.6 0.5 U black

Description

This Patch Panel by Delock can be mounted in a 19" rack. At the LSA blocks you can install up to 24 network cables with a punch down tool. The small overall height makes a high port density possible.



Item no. 43316

EAN: 4043619433162

Country of origin: China

Package: White Box

Technical details

- Connectors:
 - external: 24 x RJ45 jack
 - internal: 24 x LSA block
- For mounting in 19" racks, 0.5 U
- Cable routing 180°
- Shielded
- Cat.6
- TIA-568A/B pinout
- Cable diameter up to 0.644 mm (22 - 24 AWG)
- For solid or stranded wire
- Metal housing
- Colour: jet black RAL 9005
- Dimensions (WxHxD): ca. 482.6 x 22.23 x 78.0 mm

Package content

- 19" Patch Panel
- Installation manual
- 24 x cable ties
- 4 x screws and caged nuts
- 48 x copper foil
- Insertion Tool und Cable Stripper Delock 18411

A black, rack-mountable patch panel with 24 ports. A yellow patch cord is plugged into one of the ports.



General

Unit height:	0.5
Suitable for conductor gauge:	22 - 24 AWG
Mounting type:	19 in

Interface

External:	24 x RJ45 jack
Internal:	24 x LSA block

Technical characteristics

Category:	Cat.6
-----------	-------

Physical characteristics

Housing colour:	black
Housing material:	metal
Shielding:	shielded
Depth:	78 mm
Width:	482.6 mm
Height:	22.2 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

