

1390
Młotki z obuchami z tworzywa sztucznego
UNI 7784

	art.	Ø mm	L mm	L1 mm		 g
013900022	1390 22	22	260	70	1390/MR22	134
013900028	1390 28	28	280	85	1390/MR28	230
013900035	1390 35	35	310	95	1390/MR35	365
013900045	1390 45	45	320	107	1390/MR45	698
013900060	1390 60	60	380	128	1390/MR60	1462

