


D

diffuser D click
klosz D klik
Abdeckung D einclipsbar
diffuseur D clic



material / materiał / Material / matériel:

PMMA


opal
mleczny
opal
opaque

1000 mm	A1130038
2000 mm	A1140038
3000 mm	A1150038
4100 mm	A1160038

UNI12 BCD/U → 38
QUARTER10 BD/U6 → 120
ARC12 CD/U5 → 170
WALLE12 BCD → 180

D9

diffuser D9 click
klosz D9 klik
Abdeckung D9 einclipsbar
diffuseur D9 clic



material / materiał / Material / matériel:

PMMA

opal
mleczny
opal
opaque

1000 mm	V3490038
2000 mm	V3500038
3000 mm	V3510038
4100 mm	V3520038

VARIO30-01 ACDE-9/TY → 59
VARIO30-02 ACDE-9/TY → 60
VARIO30-03 ACDE-9/TY → 63
COMBO30-01 ACDE-9 → 70
NAMI23 CD-9 → 76
VARIO30-06 ACDE-9/U9 → 111
VARIO30-07 ACDE-9/U9 → 112
VARIO30-04 ACDE-9 → 153
VARIO30-05 ACDE-9 → 154

PMMA


end cap D9
zaślepka D9
Endkappe D9
embout D9



opal
mleczny
opal
opaque

V4980038**E**

diffuser E slide
klosz E wsuwany
Abdeckung E einschiebbar
diffuseur E coulissant



material / materiał / Material / matériel:

PC

transparent
transparentny
transparent
transparent

1000 mm	A2000116
2000 mm	A2000216
3000 mm	-

SURFACE14 EE7F/TY → 44
SURFACE14.v2 EE7F/Y → 46
LINEA20 EE7F/TY → 50
GROOVE14 EE7F/TY → 96
LINEA-IN20 EE7F/U7 → 106
CABI12 E → 122
CABI12 DUO E → 124
CORNER14 EE7F/TY → 130
CORNER12.v2 EF/U → 132
LINEA-IN20 TRIMLESS EE7F → 150

PP

frosted
szron
satinert
givré

1000 mm	A2000139
2000 mm	A2000239
3000 mm	A2000339


PP

opal
mleczny
opal
opaque

1000 mm	A2000138
2000 mm	A2000238
3000 mm	-

E7

diffuser E7 click
klosz E7 klik
Abdeckung E7 einclipsbar
diffuseur E7 clic



material / materiał / Material / matériel:

PMMA

opal
mleczny
opal
opaque

1000 mm	C1070038
2000 mm	C1080038
3000 mm	C1090038
4050 mm	C1100038

SURFACE14 EE7F/TY → 44
SURFACE14.v2 EE7F/Y → 46
LINEA20 EE7F/TY → 50
GROOVE14 EE7F/TY → 96
LINEA-IN20 EE7F/U7 → 106
CORNER14 EE7F/TY → 130
LINEA-IN20 TRIMLESS EE7F → 150

PMMA

end cap E7
zaślepka E7
Endkappe E7
embout E7



opal
mleczny
opal
opaque

C1840038