

Han CGM-P M40x1,5 D.20-26mm black



Part number	19 00 000 5188
Specification	Han CGM-P M40x1,5 D.20-26mm black
HARTING eCatalogue	https://b2b.harting.com/19000005188

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-P
Type of accessory	Cable gland

Technical characteristics

Limiting temperature	-40 ... +100 °C
Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	53
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M40
Clamping range	20 ... 26 mm
Width across corners	58.8 mm

Material properties

Material (seal)	NBR
Material (cable glands)	Polyamide (PA)
Colour (accessories)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 514B QCRV.E479780 CSA-C22.2 No. 18.3 QCRV7.E479780

Commercial data

Packaging size	1
Net weight	77.2 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27144432 Screwed cable gland (electr.)