

Active USB Type-C™ to HDMI Cable (DP Alt Mode) 4K 60 Hz 7 m

Description

This cable by Delock enables the connection of an HDMI monitor to a PC or laptop with USB-C™ or Thunderbolt™ 3 port, such as a MacBook or a Chromebook. The interface has to support the DisplayPort Alternate Mode.



Item no. 85973

EAN: 4043619859733

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB Type-C™ male >
 - 1 x HDMI-A male
- Signal direction: USB Type-C™ input > HDMI output
- Chipset: Parade PS176
- High Speed HDMI specification
- Cable gauge: 32 AWG
- Cable diameter: ca. 4.7 mm
- Contacts gold-plated
- Transmission of audio and video signals
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Supports 3D displays (1080p @ 120 Hz)
- Supports HDCP 1.3
- Supports Eyefinity
- 2 x ferrite core
- Colour: black
- Dimensions of signal amplifier (LxWxH): ca. 8.00 x 2.20 x 1.35 cm
- Length incl. connectors: ca. 7 m

System requirements

- Mac OS 10.12 or above
- Windows 8.1/8.1-64/10/10-64
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI cable

Images



General

Specification:	HDMI 2.0
----------------	----------

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x HDMI-A male

Technical characteristics

Chipset:	Parade PS176
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Ferrite core:	2 x
Pin finishing:	gold-plated
Cable gauge:	32 AWG
Diameter:	4.7 mm
Length:	7 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de