


1654
Suwmiarki noniuszowe
UNI EN ISO 13385-1DIN

	art.	A max mm	L mm	B mm	G mm	HxS mm	g
016540020	1654 200	200	330	65	0,02	20x4	370
016540030	1654 300	300	410	100	0,02	20x4	410

