

1241

Wkrętaki płaskie do pobijania



ISO 2380

	art.	SxAxL mm	L1 mm	g
012410039	1241 5,5X100	1x5,5x100	202	83
012410050	1241 6,5X125	1,2x6,5x125	240	140
012410057	1241 8X150	1,2x8x150	268	200
012410066	1241 10X200	1,6x10x200	325	270

