



## Flexible strain relief for cables model : R4/25

### Dimmension

Cable cross section (A)	4.0mm
Total length (F)	25mm
Working length (E)	20mm
Width (B)	13mm
Width (D)	9.7mm
Mounting hole (C)	Max 5.6 x 5.6mm
Maximum mounting wall thickness (G)	3mm

### Other

Material

Hydrogenated styrene butadiene block copolymer (SEBS)

Hydrogenated styrene isoprene butadiene block copolymer (SEEPS)

Ethylene Propylene Diene Monomer (EPDM)

Styrene butadiene styrene block copolymer (SBS)

