

10" Industry Hub 10 x USB 3.2 Gen 1 Type-A

Description

This solid industry capable USB hub by Delock with metal housing can be connected to a computer via the USB Type-A interface. It expands the computer by 10 USB Type-A ports. The hub can be used for automation and office applications.

USB 3.2 Gen 1 specification

With the support of USB 3.2 Gen 1 specification a data transfer rate up to 5 Gbps can be reached. Compared to USB 2.0, data can be transferred 10 times faster. All ports are backward compatible, so USB 2.0 and USB 1.1 devices can be used as well.

10" rack mounting

With the supplied mounting brackets, the hub can be mounted in a 10" rack.



Item no. 64112

EAN: 4043619641123

Country of origin: China

Package: Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) Type-B female
 - 10 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female
 - 1 x 5 V DC jack 5.5 x 2.1 mm
- Chipset: VIA VL813
- Data transfer rate up to:
 - SuperSpeed USB 5 Gbps,
 - Hi-Speed 480 Mbps,
 - Full-Speed 12 Mbps,
 - Low-Speed 1.5 Mbps
- Output power: max. 16 W total
- Robust metal housing
- Removable 10" rack brackets
- LED indicator for power
- Operating temperature: 0 °C ~ 60 °C
- Dimensions (LxWxH): ca. 215 x 135 x 45 mm
- Colour: black
- Plug & Play

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 1.0 A
- Output: 5 V / 4 A
- Ground outside, plus inside
- Dimensions:
 - inside: ø ca. 2.1 mm
 - outside: ø ca. 5.5 mm
 - length: ca. 9 mm

System requirements

- Linux Kernel 3.4 or above
- Windows 8.1/8.1-64/10/10-64
- PC or laptop with a free USB Type-A port

Package content

- Hub USB
- 1 x cable USB 3.2 Gen 1 Type-A male to USB 3.2 Gen 1 Type-B male, length ca. 1.20 m
- 2 x mounting brackets for 10" rack
- Power supply
- Screws
- Nuts
- User manual

Images



General

Unit height:	2
Function:	Hot Swap Plug & Play
Mounting type:	10 in
Supported operating system:	Linux Kernel 3.4 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit
LED indicator:	Power

Interface

Connector 1:	1 x USB 5 Gbps Type-B female
Connector 2:	10 x USB 5 Gbps Type-A female
Connector 3:	1 x DC jack

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Length:	215 mm
Width:	135 mm
Height:	45 mm
Colour:	black

Power supply

Power supply type:	Euro wall power supply
--------------------	------------------------

Power supply output:	5.0 V / 4.0 A
Power supply connector:	DC male 5.5 mm x 2.1 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

