

METAL-DETECTABLE CABLE TIE

ITEM CODE	SIZE	COLOR	MAX Ø mm	TENSILE STRENGTH (N)
FIX-MD-2.5X100	2,5x100	blue	22	80
FIX-MD-2.5X150	2,5x150	blue	35	80
FIX-MD-2.5X200	2,5x200	blue	50	80
FIX-MD-2.5X250	2,5x250	blue	65	80
FIX-MD-3.6X150	3,6x150	blue	35	178
FIX-MD-3.6X200	3,6x200	blue	50	178
FIX-MD-3.6X250	3,6x250	blue	65	178
FIX-MD-3.6X300	3,6x300	blue	80	178
FIX-MD-3.6X370	3,6x370	blue	100	178
FIX-MD-4.6X200	4,6x200	blue	50	216
FIX-MD-4.6X250	4,6x250	blue	65	216
FIX-MD-4.6X300	4,6x300	blue	80	216
FIX-MD-4.6X350	4,6x350	blue	90	216
FIX-MD-4.6X400	4,6x400	blue	105	216
FIX-MD-4.6X450	4,6x450	blue	120	216
FIX-MD-4.6X500	4,6x500	blue	150	216
FIX-MD-7.6X300	7,6x300	blue	80	540
FIX-MD-7.6X400	7,6x400	blue	105	540
FIX-MD-7.6X500	7,6x500	blue	150	540

Parameter

Installation Temperature

Working Temperature

Moisture Absorption

Material Fire Resistance (UL 94)

Resistance to

Limited Resistance

Non-Resistant

Material

COMPLIANCE

Specification

-10°C to +60°C

-40°C to +85°C

2.7% (23°C; 50% R.H.)

V-2; halogen-free

aromatic solvents, oils, greases, and their derivatives

acids

phenols and chlorinated solvents

polyamide 6.6 + metal-detectable ferromagnetic additive

EU Reg. 1935/2004, EU Reg. 10/2011, HACCP-suitable