



## BETA 1224

### Morphos screwdrivers for slotted headless screws



### Certifications and Standards



## Features

Designed to reduce fatigue and ensure high torque transmission even in the most demanding applications.

### HIGH TORQUE TRANSMISSION

The innovative tri-material handles with a rigid polypropylene core and double soft bits ensure effective and constant force transmission. Controlled deformation zones adapt to the palm contact points, improving thrust and clamping efficiency.

### CONTROL AND PRECISION

The ergonomic shape and designed index finger and thumb rests guarantee a firm grip and precise centring of the blade on the screw. Even with dirty hands or gloves, you achieve maximum directionality and safety during use.

### PERFECT GRIP AND ANTI-ROLL

The embossed texture ensures a reliable grip even under the most difficult conditions. The triangular profile prevents rolling on the work surface and promotes stable and continuous use.

### STRENGTH AND DURABILITY

The chrome-plated steel blade with sandblasted finish offers protection against corrosion and wear. The black phosphated tip ensures a precise fit with the screw and reduces the risk of slipping, prolonging the life of the tool.



### TRIMATERIAL STRUCTURE

The rigid polypropylene inner core is combined with soft, high-grip bits to ensure superior torque transmission.



### CONTROLLED DEFORMATION

The soft areas deform in a controlled manner, adapting to the point of contact and amplifying the thrust without fatiguing the hand.



### ANTI-ROTATION

The triangular shape prevents rolling on the workbench, improving safety and stability.

Dimensions



Certifications and Standards

Coded items

|  | Art.         | SxDxL<br>mm | L1<br>mm |  g |
|-----------------------------------------------------------------------------------|--------------|-------------|----------|---------------------------------------------------------------------------------------|
| 012240003                                                                         | 1224 2,5X60  | 0,4x2,5x60  | 161      | 36                                                                                    |
| 012240006                                                                         | 1224 3X75    | 0,5x3x75    | 176      | 39                                                                                    |
| 012240009                                                                         | 1224 3X100   | 0,5x3x100   | 201      | 40                                                                                    |
| 012240012                                                                         | 1224 4X100   | 0,8x4x100   | 209      | 64                                                                                    |
| 012240018                                                                         | 1224 5X125   | 1x5x125     | 234      | 76,5                                                                                  |
| 012240024                                                                         | 1224 6,5X150 | 1,2x6,5x150 | 271      | 115                                                                                   |

Scan the QR Code to access the web tab  
Specs, media and documentation in one click.

