

Han-Compact hood TE/SE M20



Part number	19 12 008 0425
Specification	Han-Compact hood TE/SE M20
HARTING eCatalogue	https://b2b.harting.com/19120080425

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Hood

Version

Locking type	Single locking lever
Size	Han-Compact®
Version	Top/side entry
Cable entry	2x M20
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	5
Net weight	33.3 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors