

USB 10 Gbps FPC Flat Ribbon Cable USB Type-C™ to USB Type-C™ 13 cm PD 5 A E-Marker

Description

This USB cable by Delock enables the connection between a device with a **USB Type-C™** connector and a PC or a laptop equipped with a free **USB Type-C™** port.

Ultra flexible cable

The cable is characterized by its special construction. Instead of normal copper wires there is a flexible circuit board inside the cable, which is also called **FPC (Flexible Printed Circuit)**. This makes the cable extremely flexible and yet robust. It is particularly suitable for charging smartphones via a power bank on the go.



Item no. 86939

EAN: 4043619869398

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 10 Gbps USB Type-C™ male
 - 1 x USB 10 Gbps USB Type-C™ male
- Chipset: VL152 E-Marker
- FPC (Flexible Printed Circuit) flat ribbon cable
- Output current: up to 5 A
- Voltage: max. 20 V
- Cable thickness: ca. 3 mm
- Data transfer rate up to 10 Gbps
- Colour: silver / black
- Length incl. connectors: ca. 13 cm

System requirements

- PC or laptop with a free USB Type-C™ port
- Device with USB Type-C™ port

Package content

- USB 10 Gbps cable

Images



General

Style:	Flat cable both sides identical
--------	------------------------------------

Interface

Connector 1:	1 x USB 10 Gbps USB Type-C™ male
Connector 2:	1 x USB 10 Gbps USB Type-C™ male

Technical characteristics

Chipset:	VIA VL152
Data transfer rate:	10 Gbps
Maximum current:	5 A
Voltage:	20.0 V

Physical characteristics

Length:	13 cm
Colour:	black silver

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de