

Technical Datasheet

tasker® K128 – 2x0,35 mm²

Balanced Microphone Cable



CATEGORY Balanced Microphone Cable (See Audio Catalogue)
APPLICATIONS Premade Audio Cables and Microphones.

- A:** Black **PVC** Sheath.
Outer cable Diam. Ø 6,00 (±0,20) mm.
- B:** Braided Shielding O.F.C. red copper covering 70%.
- C:** The cores are stranded in a pair with textile waste filler between conductors
- D:** PVC core insulation colored one red and one white.
Diam. Ø 1,55 (±0,20) mm.
- E:** Both conductors in O.F.C. red copper.
Formation 11x0,20 mm.
Nom. Cross section 2x0,35 mm².

MARKING **tasker® K128 - 2x0.35 mm² O.F.C. Low Capacitance Microphone Cable**
- Made in Italy.

CUSTOM PRODUCTION This product may be custom produced also in **L.S.Z.H.** polymer, **PE**, **PUR**, or Metallic Armored.

Cable Properties

Conductor Resistance	58 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio
Impiego		Outdoor Limited	Esterno Limitato
		Outdoor	Esterno
		Outdoor Direct Burial	Esterno Interrato

INSTALLATION	X	Fixed	Fissa
Posa	X	Restricted Mobile	Mobile Limitata
		Mobile	Mobile
		Mobile in Drag Chain	Mobile in Catena

INFORMATION	X	RoHS2 Compliant
Informazioni	X	Ver. A / 16.05.16