



EAN-13: 5901969449693  
CAT. NO: NFU-2351



## KANABO K2 MECHANICAL KEYBOARD

### PRODUCT FEATURES:

- Linear mechanical switches - smooth and consistent keystrokes without tactile feedback, designed for speed and precision
- Closed design with non-floating keys for an elegant look and stable keys
- Hot-swap sockets for easy replacement of switches without special tools or soldering
- High-quality lubricated stabilizers for smoother key operation and minimal noise
- Dedicated software for full key function customization, including macro recording
- PBT keycaps for greater resistance to wear and tear, even with heavy use
- Laser-engraved multimedia shortcuts for quick and convenient access to multimedia
- Compatible with PS4/PS5 and XBOX consoles, enjoy the freedom to play on your favorite platforms
- Anti-ghosting function, allowing you to press up to 19 keys simultaneously without interrupting the action
- Foldable feet, allowing for angle adjustment, increasing comfort of use



### PRODUCT SPECIFICATION:

Communication	Wired
Interface	USB
Key mechanism	Mechanical
Illumination color	White
Cable length	160 cm
Number of keys	87
Keys lifetime	50 mln.
Actuation point	2 mm
Actuation force	50 g
Response time	1 ms
Supported Operating Systems	Android, Windows 7, Windows 8, Windows 10, Windows 11
Platform	Android, Microsoft XBOX One S, Microsoft XBOX One X, Microsoft XBOX Series X, Microsoft XBOX Series S, XBOX One, PC, Sony PlayStation 4, Sony PlayStation 5
Included Accessories	2 spare mechanical switches, Keycap/switch puller
Dimensions	361 x 133 x 37 mm

